


LOC	DIST	REVISIONS				
H	—	P	LTR	DESCRIPTION	DATE	DWN
			F	ECR-06-021155	05 SEP 06	RC
						APVD
						MS

D

C

B


A



NOTES:

1. ATTENUATION ≤ 0.3 dB, MEASURED AT 1300nm ACC I.E.C. 61300-3-4
EQUILIBRIUM MODE CONDITION
2. FILLED OUT TEST RESULT SHEET WILL BE SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY.

PART NUMBER	"L" (meter)
0-5349582-1	0,5 -0/+0,1
0-5349582-2	1,0 -0/+0,2
0-5349582-3	1,5 -0/+0,2
0-5349582-4	2,0 -0/+0,2
0-5349582-5	2,5 -0/+0,2
0-5349582-6	3,0 -0/+0,2
0-5349582-7	3,5 -0/+0,2
0-5349582-8	4,0 -0/+0,2
0-5349582-9	4,5 -0/+0,2
1-5349582-0	5,0 -0/+0,2
1-5349582-1	5,5 -0/+0,2
1-5349582-2	6,0 -0/+0,2
1-5349582-3	6,5 -0/+0,2
1-5349582-4	7,0 -0/+0,2
1-5349582-5	7,5 -0/+0,2
1-5349582-6	8,0 -0/+0,2
1-5349582-7	8,5 -0/+0,2
1-5349582-8	9,0 -0/+0,2
1-5349582-9	9,5 -0/+0,2
2-5349582-0	10,0 -0/+0,2

1	FERRULE DUST CAP BLACK		3				
1	ST CONNECTOR ASSEMBLY		2				
L	FOCAB 0,9 62.5/125DES BLUE		1				
Qty	Description		Item				
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 01 JUL 05	tyco Electronics Tyco Electronics Nederland BV 's-Hertogenbosch, Netherlands				
DIMENSIONS: mm 		CHK A. HENGELMOLEN 05 SEP 06					
		APVD M. SCHOLTEN 05 SEP 06					
		NAME					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC —	FOMM62.5 PIGTAIL 0.9S ST				
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC —					
MATERIAL —	FINISH —	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=5349582	RESTRICTED TO —	
CUSTOMER DRAWING					SCALE NTS	SHEET 1 OF 1	REV F