

Hand-held pressure indicator - Model CPH6200

Hand-held pressure indicator - Model CPH6200

Item number: 7244946

Quantity: 1 pcs.

Order code: CPH6200-S1-ZZ1ZZHT-ZZ

Overview: Hand-held pressure indicator - Model CPH6200
Specifications according to data sheet: CT 11.01
Measuring range and accuracy: depending on connected reference pressure sensor CPT6200
Instrument version: 1 channel version with logging function , cycle and a peak value memory (Min-and Max)
Rechargeable battery and battery charger: 9 V, EU standard
Test pump: CPP1000-L, pressure range 0 ...1000 bar, hydraulic
Carrying case: for one CPH62X0, one test pump CPP1000-L and max. five CPT62X0

Details: Hand-held pressure indicator - Model CPH6200
Specifications according to data sheet: CT 11.01
Measuring range and accuracy: depending on connected reference pressure sensor CPT6200
Function: min-/ max-memory, min-/max-alarm, hold, tare, zero-point correction
Data logger functions: discrete value storage / cyclic storage
Interface: RS-232, USB via adapter cable
Power supply: DC 9 V (battery, rechargeable battery or power supply unit possible)
Standard accessories: 9 V battery, one sensor connecting cable (1.1 m) per channel
Instrument version: 1 channel version with logging function , cycle and a peak value memory (Min-and Max)
Rechargeable battery and battery charger: 9 V, EU standard
Test pump: CPP1000-L, pressure range 0 ...1000 bar, hydraulic
Carrying case: for one CPH62X0, one test pump CPP1000-L and max. five CPT62X0