



ECT SCO13-0200-050-B

E1518539

Cable Tie 200x4.8mm With Edge Clip 1-3mm Outside Serrated, Side Mount, Cross Installation

Product Properties:

Detectable	No
Min. tensile strength	230 N
Model	Internal toothing
Material quality	Polyamide (PA)
Band closure	Plastic lip/-cam
Transparent	No
Fluorescent	No
Solvable fastener	No
Text strip	None
Type of fastening	Edge clip
Colour	Black
Material	Plastic
Max. tensile force	230 N
Inflammability class of insulation material according to with UL94	Other

Dimensions:

MOQ	100 .
Unit	pcs
Length belt/tape/tie	200 mm
Band width	4.8 mm
Max. tensile force	230 N

Approvals:

MIL approval	No
VG approval	No
UL approval	No
Approved according to CE	No
With approval according to UL	No
Inflammability class of insulation material according to with UL94	Other
Approved according to DNV	No

Compliance:

CA Proposition 65	In compliance
Conflict Minerals	N/A, Contains no conflict minerals
PFAS	No PFAS
PFOA	No PFOA
PFOS	No PFOS
POPs	No POPs
REACH	No SVHC (247 Subs. 21 Jan 2025)
REACH Annex XIV	No REACH Annex XIV
REACH Annex XVII	No REACH Annex XVII
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000046 - Cable tie
ETIM-Release	10.0
Trademark	NEMIQ
Product Group	Cable tie with edge clip
Search Description	EVK2024, ENR2025V
Alternative SKU	ECTSCO13-0200-050-B
E-no	E1518539

Logistic information:

Barcode	733117641359
Country of origin	CN
E-no	E1518539
Item status	Non Stock Item, can be on stock but is not a regular stock item.
MOQ	100 .
Stock code	ECT SCO13-0200-050-B
Taric code	39269097
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se