



Pushing Performance
Since 1945

Han-Eco 10B-HBM Carrier frame



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 010 0001
Specification	Han-Eco 10B-HBM Carrier frame
HARTING eCatalogue	https://harting.com/19430100001

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® B
Type of accessory	Frame
Description of the accessory	for bulkhead mounted housings

Version

Size	10 B
------	------

Material properties

Material (accessories)	Polyamide (PA) Fibre-glass reinforced
Colour (accessories)	RAL 9005 (jet black)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)



Pushing Performance
Since 1945

Material properties

Requirement set with Hazard Levels	R22 (HL 1-2)
	R23 (HL 1-3)

Commercial data

Packaging size	1
Net weight	30.5 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140193758
eCl@ss	27440210 Fixing element for industrial connectors
ETIM	EC002310
UNSPSC 24.0	39121466