



## **Datasheet**

# RS PRO enclosure, PC, 95x65x60mm

Stock No: 197-2005



## **Technical Specifications:**

Material	Polycarbonate
Dimensions (LxWxH)	95x65x60mm
Colour	Base: RAL 7035 – light grey Cover: RAL 7035 – light grey
IP Rating	IP 65
IK Rating	IK 07/IK08
Electrical insulation	Totally insulated
Flammability Rating	UL 746C 5"

rspro.com

### **Features & Benefits:**

- Ouickly assembled with rapid hinge
- Compatible with all standard PVC enclosures
- Halogen free
- Good chemical resistance
- Temperature Range from -40° to +120°, short term
- Temperature Range from -40° to +80°, continuous
- Including:

Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

## **Dimensional line drawings**

#### TEMPO 95X65X60







