

3114 24

Crowfoot spanner

Code	ETIM
6670640	EC002130
EAN	UNSPSC
4010886667064	27-11-17-06
Country of origin	eCl@ss
Germany	21-04-01-90
Customs tariff number	
82041100	



Article description

- Angled open-end wrench for working in hard-to-reach areas
- Vanadium steel 31CrV3, chrome-plated
- No. 3114 = Delivery without pivot pin
- No. DS 3114 = supplied with rotary pin 26 D

Article information

Contents (Qty of pieces)	1	Width across flats l [mm]	24
Net weight [kg]	0,419 kg	Head height l [mm]	9 mm
Total length [mm]	250 mm	Width of head l [mm]	46,0 mm
Surface	chrome-plated	Shaft diameter	23,6 mm
Use	For working in extremely difficult to access areas	Tommy bar-Ø l	14
Material	31CrV3	Diameter l [mm]	14,00 mm
Bore Ø [mm]	14,5 mm		14,5