

EM-CSS-CONTROLSHIELD-35 - Shield connection



1276904

<https://www.phoenixcontact.com/in/products/1276904>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Shroud for control lines for 35 mm wide CONTACTRON Speed Starters



Commercial data

Item number	1276904
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	DK731Z
GTIN	4063151471385
Weight per piece (including packing)	32.4 g
Weight per piece (excluding packing)	32.4 g
Customs tariff number	73269098
Country of origin	TW

EM-CSS-CONTROLSHIELD-35 - Shield connection



1276904

<https://www.phoenixcontact.com/in/products/1276904>

Technical data

Product properties

Product type	Shroud
--------------	--------

EM-CSS-CONTROLSHIELD-35 - Shield connection



1276904

<https://www.phoenixcontact.com/in/products/1276904>

Classifications

ECLASS

ECLASS-11.0	27371392
ECLASS-13.0	27371392
ECLASS-12.0	27371392

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

1276904

<https://www.phoenixcontact.com/in/products/1276904>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

1276904

<https://www.phoenixcontact.com/in/products/1276904>

Mandatory accessories

CSS 0.37-1/3 - Speed starter

1201135

<https://www.phoenixcontact.com/in/products/1201135>



Speed starter with soft start and configurable speed for starting and reversing motors up to 230 V AC and 0.37 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, single-phase load input

CSS 0.25-1/3-EMC - Speed starter

1201520

<https://www.phoenixcontact.com/in/products/1201520>



Speed starter with soft start and configurable speed for starting and reversing motors up to 230 V AC and 0.25 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, single-phase load input, with integrated EMC filter

1276904

<https://www.phoenixcontact.com/in/products/1276904>

CSS 0.37-1/3-EMC - Speed starter

1201600

<https://www.phoenixcontact.com/in/products/1201600>



Speed starter with soft start and configurable speed for starting and reversing motors up to 230 V AC and 0.37 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, single-phase load input, with integrated EMC filter

CSS 0.25-3/3 - Speed starter

1201679

<https://www.phoenixcontact.com/in/products/1201679>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.25 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input

EM-CSS-CONTROLSHIELD-35 - Shield connection



1276904

<https://www.phoenixcontact.com/in/products/1276904>

CSS 0.37-3/3 - Speed starter

1201683

<https://www.phoenixcontact.com/in/products/1201683>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.37 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input

CSS 0.55-3/3 - Speed starter

1201694

<https://www.phoenixcontact.com/in/products/1201694>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.55 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input

1276904

<https://www.phoenixcontact.com/in/products/1276904>

CSS 0.25-3/3-EMC - Speed starter

1201713

<https://www.phoenixcontact.com/in/products/1201713>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.25 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

CSS 0.37-3/3-EMC - Speed starter

1201825

<https://www.phoenixcontact.com/in/products/1201825>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.37 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

EM-CSS-CONTROLSHIELD-35 - Shield connection



1276904

<https://www.phoenixcontact.com/in/products/1276904>

CSS 0.55-3/3-EMC - Speed starter

1201828

<https://www.phoenixcontact.com/in/products/1201828>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.55 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

CSS 0.75-3/3-EMC - Speed starter

1201829

<https://www.phoenixcontact.com/in/products/1201829>



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.75 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in