Product data sheet
Characteristics

RNG20W
Mita - rigid conduit - round - heavy gauge - white - 20 mm

TSI Code: 1568509

Price*: 4.97 GBP

Main

Range of product	Mita
Product or component type	Rigid conduit
Product specific application	Heavy duty
Colour tint	White
Quantity per set	Set of 30

Complementary

Shape	Round
Material	UPVC (unplasticized polyvinyl chloride)
Outer dimension	20 mm
Length	3 M

Environment

Standards	BS 4607 BS 6099

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	140 G
Package 1 Height	2 Cm
Package 1 width	2 Cm
Package 1 Length	100 Cm
Unit Type of Package 2	CAR
Number of Units in Package 2	90
Package 2 Weight	12.98 Kg
Package 2 Height	12 Cm
Package 2 width	13 Cm
Package 2 Length	300 Cm
Unit Type of Package 3	PAL
Number of Units in Package 3	9000
Package 3 Weight	1373 Kg
Package 3 Height	140 Cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Package 3 width	120 Cm
Package 3 Length	300 Cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

Contractual warranty

Warranty	18 months

Product Life Status : Commercialised