



Holder Style
HC-49/U HC-43/U

Adjustment Tolerance:	±30 PPM
Adjustment Temp:	25 °C
Temp. Stability:	±50 PPM
Op. Temp. Range:	-10 °C to +60 °C
Load Capacity:	30 pF
Circuit Mode:	Fundamental
Circuit Condition:	Parallel
Max. ESR:	50 Ω
Drive Level:	500μW
C0:	7.0pF Max
C1	Not Specified
L1	Not Specified
Pulling:	Not Specified
Ageing:	<±5PPM 1 st Year



Certificate No. 733/95

FREQUENCY: 12.000000 MHz

AEL PART NUMBER: 4088