

## TORCH 150 x 10 Tpi - 5 pcs | Metal: Heavy duty TORCH™ demolition blades



- Strong: Robust 1.06 mm thick body.
- Shatter resistant: The bi-metal blade body will bend and flex but not break.
- Torch: - Thick 1.06 mm robust blade body for precise cuts in sheet metal and pipes.
- 25 mm blade height for improved stability and minimum vibration.

Article Number	48005712
Blade length (mm)	150
Material type	Bi-Met,Co
Max. cutting capacity inox [mm]	4 - 10
Max. cutting capacity metal pipe	10 - 100
Max. cutting capacity non ferrous metals [mm]	4 - 10
Max. cutting capacity steel (mm)	4 - 10
Max. cutting capacity wood with nails [mm]	Yes
Pack quantity	5
Ref. No.	-
Rescue	Yes