

Corner protection profile C35 magnetic

Article number	1112130	Sales unit quantity	5 Piece
Colour	Yellow / black	Sales unit EAN	4005546742328
Packaging unit	5 pieces / pack	Packing weight (gross)	3728 G
Base EAN	4005546742342	Country of origin	DE



Product description

- Magnetic flexible corner protection profile made of polyurethane foam
- For indoor use only
- Ideal for use in production areas, shipping department and warehousing, basements, staircases, garages, on walls and joists, shelves and cabinets as well as on machines, storage trolleys etc.
- Marks danger spots, protects surfaces, walls and mitigates impact injuries
- Colour according to ASR A1.3 similar to RAL 1004/9003 (signal yellow/signal black)
- Fire test according to DIN EN 13501-1:2018-12 class E
- Temperature resistant from -30°C - + 70°C
- Application temperature: from -30°C - + 70°C
- Profile length: 1 m
- Inner surface: 35 mm on each side

Product features

Outer width (mm)	45
Outer height (mm)	45
Outer depth / length	1,000 mm
Brand	DURABLE
Inner width (mm)	35

Corner protection profile C35 magnetic

Inner height (mm)	35
Material thickness	10 mm
Special colour	Similar to RAL 1003 signal yellow / 9004 signal black
Colour	Yellow / black
Application area	Indoor area, protected outdoor area
Mounting type	Magnetic