

## 910.11 ST G1/2B / G1/2 union nut DIN 16270

### DIN-Shut-off valve

Item number: 9095101

Quantity: 1 pcs.

Order code: 910.11-SB11CB-ZZZ-P12-ZZ 0

Overview: 910.11 ST G1/2B / G1/2 union nut DIN 16270

DIN-Shut-off valve

Material body: Carbon steel

Version: without test connection, per DIN 16270 or similar (with vent screw)

Connection process side + instrument side: G 1/2 B male + G 1/2 with nipple and union nut

Design: Form B, with nipple and union nut as well as shaft for mounting bracket

Material packing: PTFE

Permissible medium temperature: -10...+120°C

Nominal pressure: PN max. 400 bar

Details:

DIN-Shut-off valve

Specifications according to data sheet: AC 09.02

Version: without test connection, per DIN 16270 or similar (with vent screw)

Material body: Carbon steel

Material packing: PTFE

Permissible medium temperature: -10...+120°C

Nominal pressure: PN max. 400 bar

Design: Form B, with nipple and union nut as well as shaft for mounting bracket

Connection process side + instrument side: G 1/2 B male + G 1/2 with nipple and union nut