

Laserliner®

VideoFlex G3 Ultra

SnakeCamera G3 10 m



10 m
DOF 1...6 cm

Professional video inspection system
for visually inspecting areas that are
difficult to access – also
over great distances



- **The camera head at a FlexCamera** transfers pictures directly to a LCD-Monitor.
- **Problem locating:** the camera indicates what is behind or in objects, walls circuits or cables etc. even under worst light conditions, due to the LED-lighting.
- **REC-Function:** still picture and video can be recorded for a later analysis.
- **Waterproof camera head and cable**
- **Ideal for difficult accessibly areas** due to the small measuring head (ø 9 mm)
- **Camera unit can be replaced** to suit application
- Powerful object lighting thanks to **4 high-performance LEDs**
- **Extraneous light reduction:** contrasty LC-Display which provides an optimum display even under light irradiation.
- External monitors operated via **TV Out connection**
- **Formattable SDHC-Card**
- **Rotation:** The manual image rotation function enables the image to be rotated by 180° on the monitor.
- **Mirror function** for correcting mirror-inverted images.

TECHNICAL DATA

| |
|--|
| CAMERA HEAD / CABLE ø 9 mm, IP 68 (immersion depth 2 m, 60 min.) |
| CAMERA FOCUS F1 cm - F6 cm |
| SCREEN TYPE 3.5" TFT colour display |
| CAMERA RESOLUTION 640 x 480 pixel |
| RESOLUTION DISPLAY 320 x 240 pixel |
| RESOLUTION PICTURE / VIDEO 720 x 480 pixel |
| FORMAT PICTURE / FORMAT VIDEO JPEG / AVI |
| LED 10 luminosity degrees |
| ZOOM 1.5 x digital zoom in 10% steps |
| MEMORY Supports up to max. 8 GB SDHC card |
| LENGTH OF FLEX CABLE 10 m |
| PORT Mini USB |
| CONNECTIONS Micro-SD, Analog-video |
| POWER SUPPLY Li-Ion pack battery 3.7V / 1.7Ah / 5V / 1A power supply unit |
| CHARGING TIME approx. 4 h |
| OPERATING TIME approx. 4 h |
| OPERATING TEMPERATURE 0°C ... 45°C |
| STORAGE TEMPERATURE -10°C ... 60°C |
| WEIGHT (incl. batteries and flexcamera) 1.6 kg |



Camera head (ø 9 mm) with LED-Lighting



3.5" TFT colour display



Magnetic Pocket-star LED flashlight. 40 x wipes (Exclusive RS)



VideoFlex G3 Ultra

- inclusive carrying case
+ SnakeCamera G3 10 m
+ TopClips G3
+ TopGuide G3
+ Li-ion battery pack
+ Power supply unit/charger with internal adapter
+ software
+ USB/REC cable
+ 4 GB micro-SD card
+ Video cable

Packing dimension (W x H x D)
450 x 375 x 125 mm

| ARTICLE | ARTICLE NO. | EAN CODE | PU |
|--------------------|-------------|-----------------|----|
| VideoFlex G3 Ultra | 088.810A | 4 021563 695003 | 2 |

CAMERA 640 x 480 pixel LED LIGHT IP 68

DISPLAY 320 x 240 pixel 3.5" LCD 180° ZOOM 1.5x

REC SD USB Li-Ion Battery

RECHARGE HARD