




THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS



SPECIFICHE DI CARICO:
 Componente spessore 4,0 mm forza F=20N min
 Componente spessore 4,5 mm forza F=25N min
 Componente spessore 5,0 mm forza F=30N min

NOTA:
 DISEGNO PROVVISORIO (VALIDO PER PRODUZIONE) REALIZZATO DA
 SCANSIONE OTTICA DEI PEZZI CAMPIONATI CON QUOTE AL NOMINALE
 SEGUIRA' DISEGNO FORMALMENTE CORRETTO

AAVID THERMALLOY
 EUROPE www.avidthermalloy.com

Via XXV Aprile, 52
 40087 Cadriano - Bologna ITALY
 Tel. +39 051 784011
 Fax +39 051 784080

Cheney Manor
 SWINDON WILTS GNR1 4RN UK
 Tel. +44 1793 401400
 Fax +44 1793 813888

COMPANY WITH QUALITY SYSTEM CERTIFIED BY DNV ISO 9001

COMPANY WITH QUALITY SYSTEM CERTIFIED BY BSI ISO 9002

Die n.	MATERIAL EN10132-4 C67S 0.35 x 4
Factor	GENERAL TOLERANCES
Part n.	
Area mm ²	FINISH Zincatura bianca alta resistenza
Weight	Tratt.termico: BONIFICA 42-46 HRC
Notes	
Drawn	S.Melotto
Check	

REV	Date	Revision description	SE
A	25Sep07	ORIGINAL (was ZA3899)	By

DRAWING n.		439647	
Vis. n.			
Description: 5901G Spring clip			
Format	Scale	1	
A4	1:1		

all dimensions in mm (ins)