



DWG NO  
C-179228

THIS DRAWING IS A CONTROLLED DOCUMENT.

USED ON



- NOTES:
- 1 MATERIAL : 66 NYLON (UL94V-0)
  - 2. PRODUCT SPEC.: 108-5408
  - 3. APPLICATION SPEC.: 114-5179
  - 4 7-179228-3 WAS OBSOLETE.
  - 5 CAVITY NUMBER LOCATED. (OPTIONAL)



7-179228-5	5-179228-5	3-179228-5	1-179228-5	15	28	30.8	32.0
7- 4	5- 4	3- 4	1- 4	14	26	28.8	30.0
7- 3	5- 3	3- 3	1- 3	13	24	26.8	28.0
7- 2	5- 2	3- 2	1- 2	12	22	24.8	26.0
7- 1	5- 1	3- 1	1- 1	11	20	22.8	24.0
7- 0	5- 0	3- 0	1- 0	10	18	20.8	22.0
6- 9	4- 9	2- 9		9	16	18.8	20.0
6- 8	4- 8	2- 8		8	14	16.8	18.0
6- 7	4- 7	2- 7		7	12	14.8	16.0
6- 6	4- 6	2- 6		6	10	12.8	14.0
6- 5	4- 5	2- 5		5	8	10.8	12.0
6- 4	4- 4	2- 4		4	6	8.8	10.0
6- 3	4- 3	2- 3		3	4	6.8	8.0
6-179228-2	4-179228-2	2-179228-2	179228-2	2	2	4.8	6.0
BLACK	YELLOW	BLUE	NATURAL	POS	A	B	C

PART NUMBER		POS	A	B	C
DWN	12NOV1993	MATERIAL	SEE NOTE 1		
T.FURUYA		HEAT TREAT	-		
CHK	15NOV1993	Tyco Electronics Corporation Shanghai, P.R.China, 200233			
S.KUBOUCHI					
APVD	15NOV1993				
S.KUBOUCHI		NAME			
CRIMP TYPE II RECEPTACLE HOUSING (AMP CT CONNECTOR 2mm PITCH)					
SCALE	SIZE	DRAWING NO	SHEET	OF	REV
NTS	A3	C-179228	1	1	B1

GENERAL TOLERANCE

0 < A ≤ 10	±0.2
10 < A ≤ 30	±0.25
30 < A ≤ 100	±0.3
ANGLES	±3°

B1	REVISED ECR-08-032323	19DEC08	D.S	S.Y	
P	LTR	REVISION RECORD	DATE	DWN	APVD

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	± .
1 PLC	± .
2 PLC	± .
3 PLC	± .
4 PLC	± .

ANGLES ± 3°

SURFACE TEXTURE

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

LOC  
ES  
DIST  
00

3306-7 (1/08)

8 7 6 5 4 3 2 1