


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL ISSUE	13 SEP 05	MGR	DB



NOTES:

- 1 ATTENUATION  $\leq 0,3$  dB, MEASURED AT 1300nm ACC. TO IEC 61300-3-4 EQUILIBRIUM MODE CONDITION
- 2 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- 3 CABLE INFO:
  - CORE DIA - 50/125  $\mu$ m
  - OUTER DIA - 2,5 mm
  - JACKET COLOR - ORANGE
  - JACKET MATERIAL - LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349560-Y	XY,0
4-5349560-1	1,5 -0/+0,2
9-5349560-1	15,5 -0/+0,2

Qty	Part Number	Description	Item
2	-	PROTECTIVE COVER, 2.5MM, BLACK	5
2	-	KIT, MM, CER, ASSY, BULK	4
2	-	CRIMP EYELET, BRIGHT TIN	3
2	-	FOAC STRAIN RELIEF 2,5 BAY BLACK	2
L	-	FOCAB 2.5S 50/125 ORANGE LSZH	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13 SEP 05 GIRIYAPPA. M	Tyco Electronics Corporation FOBU, Bangalore, India	
DIMENSIONS: mm		CHK 13 SEP 05 DIWAKAR BELAVADI	NAME	
		APVD 13 SEP 05 DIWAKAR BELAVADI	FOMM50 LEAD 2,5S ST - ST	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE	CAGE CODE
0 PLC	± -	APPLICATION SPEC	A2	00779
1 PLC	± -	WEIGHT	DRAWING NO	
2 PLC	± -	SCALE	C=5349560	
3 PLC	± -	CUSTOMER DRAWING	NTS	SHEET 1 OF 1
4 PLC	± -	FINISH	REV	A
ANGLES	± -			

C-5349560