




Pushing Performance

Han Split Hood 24 B



Part number	09 30 024 0408
Specification	Han Split Hood 24 B
HARTING eCatalogue	https://b2b.harting.com/09300240408

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® B
Type of hood/housing	Panel feed through housing

Version

Locking type	Double locking lever
Size	24 B
Version	Top entry
Cable entry	4x Integrated
Field of application	Standard hoods/housings for industrial connectors
Details	Please order cable entry seals separately.
Pack contents	2 split hood halves

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP54 when mounted vertically IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12
Cable diameter	17.8 mm

Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7037 (dust grey)



Pushing Performance

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	1
Net weight	54.6 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors