

# ClimaSys PTC heating resistance 100W, 12-24V insulate

NSYCR100WU1C

EAN Code: 3606480152313

Price: 146,80 EUR

### Main

Range	ClimaSys	
product name	ClimaSys CR	
Product or component type	Resistance heater	
Power range	100 W	
Input voltage	1224 V AC/DC 50/60 Hz	
Electrical connection	4 screw terminals 2.5 mm <sup>2</sup>	

## Complementary

Operating position	Vertical	
Ambient air temperature for operation	-4070 °C	
IP degree of protection	IP20	
Electrical insulation class	Class II	
Product certifications	VDE	
Material	Body: extruded aluminium Cover: plastic	
Height	External: 150 mm	
Width	External: 60 mm	
Depth	External : 90 mm	
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure	
Fixing mode	By clips	
Mounting support	35 mm DIN rail	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	10.000 cm
Package 1 Length	13.000 cm
Package 1 Weight	360.000 g

# **Contractual warranty**

Rates duty January 2016

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

## Environmental footprint

Environmental Disclosure

Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	60bb7229-9ac3-41cb-896e-a93aa448ebf8

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins