

## COMPACT-MOBIL ELECTRONIC SERVICE CASE

The trolley case with special tools for the assembly and maintenance of electronic devices

7000 **BERNSTEIN COMPACT-MOBIL** with tool assortment 7010, 7020 and 7030

7015 **BERNSTEIN COMPACT-MOBIL** without tools

7100 **BERNSTEIN COMPACT-MOBIL** with tool assortment 7010, 7020 and 7060

### Description:

Elegant case made from deep-drawn, impact-resistant, grained dark brown plastic with a continuous bronze anodised aluminium frame, dustproof and rainproof, acid-resistant, scratch-resistant and non-slip. For energy saving transport stable rolls are installed and a telescopic handle is mounted.

The arrangement of the rolls results in a vibration absorbing locomotion. The tools are held in their partitions.

The case has 3 removable tool trays: No. 7010, 7020 and 7030. The trays contain 63 tools. On request the tray No. 7030 may be exchanged for No. 7060 (VDE-tools). The lid of the case has a pocket for documents etc.

The plastic tray with adjustable partitions in the bottom allows a clear arrangement of a soldering iron, measuring instruments and accessories of various sizes.

The case has two locks.

**Outside dimensions: 500 x 400 x 200 mm**

**Weight without tools: approx. 8.000 kg**

**Weight with tools 7000: approx. 10.600 kg**

**Weight with tools 7100: approx. 10.700 kg**

### Tool set:

No.	Description of individual tools	No.	Description of individual tools
	<b>Tool tray No. 7010</b>	2-295	<b>Hand magnifier</b> with light
2-155	<b>Claw-type gripper</b> with 3 wire claws and clip	3-565	<b>Water pump pliers</b> , 130 mm, chrome-plated
2-601	<b>IC-tweezers</b> , nickel-plated, 125 mm, for gripping, inserting and removing IC's	3-715-1	<b>Combination pliers</b> , 115 mm, chrome-plated, BERNSTEINIT-insulation
2-620	<b>PLCC-extractor</b>	4-141	<b>Screwdriver</b> , with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 75 x 3.5 mm, with black tips
2-655	<b>Pocket inspection lite</b> with fibre optic adaptor for close inspection of small, tight, hard-to-see areas	4-142	<b>Screwdriver</b> , as above, 100 x 4.0 mm
3-654-14	<b>EUROline-side-cutters</b> , 120 mm, for hard wire up to 0.4 mm Ø, for copper wire up to 1.5 mm Ø, with slim rounded head, box joint, double leaf spring, bright burnished, with bicoloured hand-guard	4-271	<b>Cross-recess screwdriver</b> , Pozidriv, size 0, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tips
3-672-14	<b>EUROline-end-cutters</b> , 130 mm, for copper wire up to 0.6 mm Ø, cutting edge 20° angular, box joint, double leaf spring, bright burnished, with bicoloured hand-guard	4-272	<b>Cross-recess screwdriver</b> , Pozidriv, size 1, as above
3-682-14	<b>EUROline-flat nose pliers</b> , 130 mm, extremely slim, box joint, double leaf spring, bright burnished, with bicoloured hand-guard	4-351	<b>Offset screwdriver</b> , 100 x 5 mm, nickel-plated, chrome vanadium
3-683-14	<b>EUROline-snip nose pliers</b> , 130 mm, extremely slim, box joint, double leaf spring, bright burnished, with bicoloured hand-guard	4-407	<b>Retaining screwdriver</b> , 110 x 4 mm
4-161	<b>Electronics screwdriver</b> with special handle and swivel top, blade chrome vanadium, chrome-plated, with black tip, 40 x 1.0 mm	5-161	<b>Clamping scissors</b> , 130 mm, stainless
4-162	<b>Electronics screwdriver</b> as above, 40 x 1.5 mm	5-301	<b>Special scissors</b> , with serration, 110 mm, nickel-plated
4-163	<b>Electronics screwdriver</b> as above, 40 x 2.0 mm	6-771	<b>Adjustable wrench</b> , jaws opening 0 - 12 mm, total length 100 mm
4-164	<b>Electronics screwdriver</b> as above, 50 x 2.5 mm	6-964 L	<b>TORX-Screwdriver</b> , size T 9, with hole, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tip
4-165	<b>Electronics screwdriver</b> as above, 50 x 3.0 mm	6-965 L	<b>TORX-Screwdriver</b> , size T 10, with hole, as above
4-281	<b>Electronics cross-recess screwdriver</b> as above, size 000	6-966 L	<b>TORX-Screwdriver</b> , size T 15, with hole, as above
4-282	<b>Electronics cross-recess screwdriver</b> as above, size 00	7-425	<b>Dust brush</b>
4-283	<b>Electronics cross-recess screwdriver</b> as above, size 0		
4-284	<b>Electronics cross-recess screwdriver</b> as above, size 1		<b>Tool tray No. 7030</b>
5-006	<b>Component tweezers</b> , 140 mm, with insulated jaws, for easy insertion and removal of plug-in transistors of various sizes, nickel-plated	3-133-1	<b>Side cutters</b> , 145 mm, for hard wire up to 1.25 mm Ø, for soft wire up to 2.5 mm Ø, chrome-plated, with BERNSTEINIT-insulation
5-049	<b>Watchmaker's tweezers</b> , sharply-pointed, 110 mm, stainless	3-235-1	<b>Telephone pliers</b> , 160 mm, chrome-plated, with BERNSTEINIT-insulation
5-107	<b>Engineer's tweezers</b> , made from steel, with bent tips, 150 mm, nickel-plated	3-732-1	<b>Combination pliers</b> , 165 mm, chrome-plated, with BERNSTEINIT-insulation
5-115	<b>Heat dissipating tweezers</b> , for use when soldering transistors, gold-bonded diodes etc., 165 mm, nickel-plated	4-143	<b>Screwdriver</b> , to DIN 5265, special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tip 125 x 5.5 mm
5-117	<b>Engineer's tweezers</b> , straight-flat-wide, 145 mm, nickel-plated	4-144	<b>Screwdriver</b> , as above, blade 150 x 6.5 mm
5-191	<b>ESD tweezers</b> , 120 mm, conductive, rounded tips	4-145	<b>Screwdriver</b> , as above, blade 150 x 8.0 mm
5-194	<b>ESD tweezers</b> , 120 mm, conductive, bent pointed tips	4-256	<b>Cross-recess screwdriver</b> , as above, size 1, with black tip
		4-257	<b>Cross-recess screwdriver</b> , as above, size 2, with black tip
		4-344 VDE	<b>Voltage tester</b> , for 220 - 250 V, blade 100 x 3.5 mm
		5-0605	<b>Universal stripping tool</b>
		6-105	<b>Socket wrench</b> , with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 5.5 mm A/F
		6-107	<b>Socket wrench</b> , as above, 7.0 mm A/F
			<b>To complete the set we recommend for the bottom of the case:</b>
		5-240	<b>Warding file set</b> , 6 pieces, with wooden handles, in a wallet
		6-820	<b>Set of allen hex sockets</b> , 8 pieces, 1.5 - 6.0 mm
		7-512	<b>Miniature caliper square</b> , measuring range 75 mm, stainless
		8-135	<b>ERSA Multitip soldering iron</b> , 15 W/230 V
		8-390	<b>Desoldering pump</b> , length 195 mm, 20 mm Ø
		9-325	<b>Plastic box</b> , with hinged lid and adjustable compartments, 200 x 130 x 30 mm
	<b>Tool tray No. 7020</b>		
1-735	<b>Adjusting screwdriver handle</b> , double-ended		
1-738	<b>Special hard plastic bit</b> , 1.5 x 0.5 mm		
1-739	<b>Special hard plastic bit</b> , 3.0 x 0.5 mm		
1-909	<b>Engineer's mirror</b> with handle, made entirely from BERNSTEINIT		
2-126	<b>Desoldering bar</b> , slotted at one end, with plastic handle		
2-127	<b>Tin knife</b> with plastic handle, 115 mm		
2-132	<b>Spring hook</b> , nickel-plated and insulated, 175 mm		
2-161	<b>Magnetic bar</b> with double ball- and socket joint, 215 mm		
2-166	<b>Glass fibre contact cleaner</b>		
2-265	<b>2 test prods</b> , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire		

# COMPACT-MOBIL 70000 ELECTRONIC SERVICE CASE

The trolley case as bordcase for world-wide service



## The service-case

- with high quality tools for electronics
- with telescopic handle, length up to 950 mm
- mobile on installed stable rolls

