

**910B/SN**
**chiavi a bussola snodate con attacco quadro femmina 3/8" bocca poligonale, cromate**



art.	art.	mm	Ø mm	L mm	Ø1 mm	A mm	g
009100230	910B/SN 10	10	14,5	48,5	19	8,8	60
009100231	910B/SN 11	11	15,8	49,5	19	9,8	61
009100232	910B/SN 12	12	17,0	50,0	19	10,3	62
009100233	910B/SN 13	13	18,3	51,0	19	11,3	64
009100234	910B/SN 14	14	19,5	51,0	19	11,3	63
009100235	910B/SN 15	15	20,8	53,5	19	12,8	69
009100236	910B/SN 16	16	22,0	53,5	19	12,8	71
009100237	910B/SN 17	17	23,3	54,5	19	13,8	74
009100238	910B/SN 18	18	24,5	54,5	19	13,8	77
009100239	910B/SN 19	19	25,8	56,5	19	13,8	83