



1120 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Peli™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Peli cases have survived. Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **Watertight, crushproof, and dustproof**
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Pick N Pluck™ with convoluted lid foam
- Peli's legendary lifetime guarantee**
- * Where applicable by law



CONFIGURATIONS



1120
Standard



1120NF
No Foam



1120WF
With Foam

DIMENSIONS

Interior (L×W×D)	7.29 x 4.78" x 3.33 (18.5 x 12.1 x 8.5 cm)
Exterior (L×W×D)	8.41 x 6.76" x 3.87 (21.4 x 17.2 x 9.8 cm)
Lid Depth	0.50" (1.3 cm)
Bottom Depth	2.56" (6.5 cm)
Total Depth	3.06" (7.8 cm)
Int Volume	0.07 ft³ (0.002 m³)
Padlock Hole Diameter	0.19" (0.5 cm)

MATERIALS

Body	Polypropylene
Latch	Polypropylene
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLOURS

 Black	 Orange	 OD Green	 Yellow
---	--	--	--

WEIGHT

Weight With Foam	1.43 lbs (0.6 kg)
Weight Empty	1.34 lbs (0.6 kg)
Master Pack Weight	10.45 lbs (4.7 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	210°F (98.9 °C)

CERTIFICATIONS

IP67
Def Stan 81-41

OTHER

Master Pack	6
Military	yes

ACCESSORIES

				
1121 3 pc. Replacement Foam Set	1123 Replacement O-ring	1120PF Special Application Panel Frame	1507 Quick Mounts - set of 4	1506TSA TSA Lock
				
1500D Desiccant Silica Gel				