PRODUCT-DETAILS

GMN-M25

LOCKNUT PA6 M25X1.5 GRY

General Information

Extended Product Type:	GMN-M25
Product ID:	7TAA292670R0066
EAN:	7630030234019
Catalog Description:	LOCKNUT PA6 M25X1.5 GRY
Long Description:	Gray Hexagonal Lock Nut with Metric Threads, Material - Polyamide 6, Thread Size - M25x1.5
Display Name:	GMN-M25

Additional Information

Product Main Type:	PMA Flexible Cable Protection
Application:	Suitable for a Wide Range of Applications
Product Type:	Hexagonal Lock Nut

Ordering

© 2026 ABB. All rights reserved.

EAN:	7630030234019
UPC:	786209956958

Technical

Number of Batteries:	0
Color:	Gray

Environmental

WEEE Category:	Product Not in WEEE Scope

Container Information

Package Level 1 Units:	100 EA
Package Level 1 EAN:	7630030234019
Package Level 1 Height:	0 mm 0 in
Package Level 1 Depth / Length:	0 mm 0 in
Package Level 1 Width:	0 mm 0 in

Certificates and Declarations

Data Sheet, Technical Information:	GMN-M25
Instructions and Manuals:	GMN-M25
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC000940 - Locknut for cable screw gland
ETIM 9:	EC000940 - Locknut for cable screw gland
UNSPSC:	31161716

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

© 2026 ABB. All rights reserved.



© 2026 ABB. All rights reserved.