



### Main

Range of product	Altira
Product or component type	Socket-outlet
Device presentation	Mechanism
Number of power socket outlets	1 2P + E French
Outlet standard description	Pin earth
Socket additional information	Rotoclip Shuttered
Colour tint	Polar white (RAL 9003) cover plate

### Complementary

Product destination	Fixing frames
Range compatibility	OptiLine 45 OptiLine 70 with Altira adaptor
Ground lug position	Pivoting Slanted 45° position Straight 90° position
Rated current	16 A - 250 V - AC - 50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Connections - terminals	Screwless terminals
Number of cables	4 x 1.5...2.5 mm <sup>2</sup> for solid stranded cable(s) 4 x 1.5...2.5 mm <sup>2</sup> for rigid cable(s)
Material	PC for mechanism cover
Surface treatment	Untreated
Surface finish	Satin
Product compatibility	Altira fixing frame
Standards	EN 60529 EN 62262 IEC 60884-1 NF C 61-314
Height	45 mm
Width	45 mm
Depth	39 mm

### Environment

Ambient air temperature for operation	5...50 °C
Ambient air temperature for storage	-15...60 °C
IK degree of protection	IK08
IP degree of protection	IP44
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid Hydrogen peroxide (H2O2)
Environmental health and issues	Halogen free