

FEATURES

- Extends out from the wall and allows your monitor or television to turn 60° left or right
- Wide wall plate for confidence in your installation
- Post-installation level adjustment to ensure a perfect level
- VESA compliant

RS PRO VESA Wall Mount With Extension Arm, For 90in Screens

RS Stock No.: 141-8312



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From the trusted RS PRO brand solid articulating wall mounting bracket is a stable, flexible adjustable wall mounting for your TV monitor. The TV brackets have a wide plate and have post-installation level adjustment allows the TV to "roll" up to 3° clockwise and anti-clockwise to ensure it is at an ideal viewing level.

General Specifications

Mounting Surface	Wall
Extension Arm	Yes
Maximum Load	75kg
Level Adjustment	3° to -3°
Swivel	60° to -60°
Tilt	5° to -15°
Rotation	120° (arm & display)
Material	Iron
Colour	Black
Applications	TV wall brackets are an ideal way to maximize the available space in a room while optimally displaying a flat panel screen



Mechanical Specifications

Screen Size Capacity	127cm to 228.6cm
Maximum Screen Size	228cm
Minimum Screen Size	127cm
Height	630mm
Width	885mm
VESA Configurations	200 x 200 mm, 300 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 600 x 400 mm, 800 x 400 mm
Minimum Distance From the Wall	69mm
Maximum Distance From the Wall	635mm

Approvals

Standards Met	VESA standard
---------------	---------------





