



Part Number : [1300060839](#)

Product Description : Mini-Change A-Size Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 18 AWG, Yellow PVC Cable, 5.0m (16.40') Length

Series Number : 130006

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : 104000A05M050



Documents & Resources

Drawings

[1300060839 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 18 AWG, Yellow PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	78678841628

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	5.6A
Voltage - Maximum	300V

Physical

Cable Diameter	7.14mm (.281")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded

Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	180.720/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	AWM 2661
Wire Size (AWG)	18