

**ARCANOL-TEMP90-1KG** [↗](#)

Bearing grease

High-temperature grease ARCANOL-TEMP90

Technical information

Your current product variant

Grease category	HT	High-temperature greases
Package size	1 KG	1 kg can

Technical data

$\vartheta_{O \min}$	-40 °C	Operating temperature, min.
$\vartheta_{O \max}$	160 °C	Operating temperature, max.
ϑ_G	90 °C	Upper continuous limit temperature
$n \cdot d_M$	700.000 mm/min	Speed of rotation specific value
	Polycarbamide	Thickener type
	Mineral oil	Base oil type
ν_{40}	148 mm ² /s	Base oil viscosity at +40°C
ν_{100}	15,5 mm ² /s	Base oil viscosity at +100 °C
	3	NLGI class
	High-temperature grease	Grease category
ρ	0,9 kg/dm ³	Density
	1 kg can	Container
$\approx m$	1,084 kg	Weight