



Technical data

1R12X15X125

Inner rings

Needle roller bearing, inner ring

PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	12 mm
B - Bearing/Inner ring width	12,5 mm
F - Under roller diameter	15 mm
rs - Min fillet radius	0,3 mm
Lubrication hole on inner ring	Non/No
t - IR chamfer length	1 mm
Precision class	P0
Mass	0,006 kg

ABUTMENT	
da min - Min shoulder diameter IR	14 mm
ras max - Max shaft & housing fillet radius	0,3 mm