

Eaton 24FDIHA5

Catalog Number: 24FDIHA5

Fuse-link, medium voltage, 5 A, AC 22 kV, 51 x 565 mm, full-range, BS, with striker

General specifications



| Product Name | Catalog Number |
|--|----------------|
| Eaton Bussmann series medium voltage BS air fuse | 24FDIHA5 |
| | EAN |
| | 5027590468947 |
| Product Length/Depth | Product Height |
| 590 mm | 50.8 mm |
| Product Width | Product Weight |
| 50.8 mm | 2724.667 g |
| Certifications | |
| BS 2692-1 | |

Product specifications

Resources

Used with

A3354710 Fuse clip

Type

fuse

Application

protection of primary side
transformers
used in fuse switch
combination units, fuse
bases and fuse switches

Amperage Rating

5 A

Fuse size

50.8 x 565 mm

Breaking capacity

35.5 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Full-range

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class full-range

Fuse shape

Cylindrical

Pre arc (I₂T)

5.9 x 101

Resistance

412 ohms

Fuse diameter

51 mm

Interrupt rating

35.5 kAIC

Construction size

51 x 565 mm

Mounting method

Clip-in

Voltage rating

24 kV

Fuse type

FDIH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia