



tested to work



20501-231 Outer Shell Jacket

breathable - wind- and waterproof

MASCOT® SAFE SUPREME



100% polyester

210 g/m²



Ripstop. The product is according to EN ISO 20471 certified to retain its qualities with 50 domestic washes. Hydrostatic pressure test > 10,000 mmH₂O according to EN ISO 811.

Industrial care category B3



- Breathable, wind and waterproof with taped seams.
- Reinforcements inside the jacket, so the lining does not tear when you have tools in the trouser pockets.
- Durable CORDURA® - reinforcement at the wrist to extend product life.
- Waterproof extension at the back that can be folded down in the rain and cold.
- Mesh with ventilation under the sleeves - opens with zip.

Technical info

Fluorescent and with vertical and oblique, transverse reflective strips. Breathable, wind and waterproof. Taped seams. Lining in mesh material. Detachable lined hood can be adjusted to fit over a helmet via drawstring. Adjustable wire on both sides of the hood. Mesh with ventilation under sleeves - opens with zip. High collar. Ribbed inner collar. Waterproof pen pocket on the sleeve. Fastening with zip and storm flap with press studs. Zipped inner pockets under storm flap - one designed especially for a mobile with holes for headset wire and guide loops to keep wire accessible. Zipped pocket under storm flap large enough to hold a 7-inch tablet. Flap on back of jacket can be folded up for standard back length or released for extended back. Chest pocket with zip. D-ring. Ergonomically shaped sleeves allow for high freedom of movement. Ribbed inner waistband to keep the cold out. CORDURA® fabric reinforced cuffs with press stud fastening. Front pockets with zip.

User



CORDURA
F A B R I C

Certifications



HIGH-VIS
GROUP:

A

EN ISO20471



EN343



4
X

RIS-3279-TOM



Logo

The product is certified with maximum 0,2000m² logo area. This approved area must not be exceeded. Logo on, respectively, front or back of the product can constitute only a maximum of 50% of the total approved logo area in order to maintain the EN ISO 20471-certification. Note: The listed area is only a guide to how much space is available for logo placement. In order to maintain the product's hi-vis class according to EN ISO 20471, the instructions on logo size must be observed.

Logo placement:

- Workwear logo. Left breast. Max 6x7 cm/2.3x2.7 inches
- Workwear logo. Mid-back. Max 25x20 cm/9.8x7.8 inches
- Workwear logo. Horizontal on right sleeve. Max 10x5 cm/3.9x1.9 inches
- Workwear logo. Special placement. Contact to discuss further

