

TM171DWAL2U

Modicon M171 Optimized Wall thermostat without backlight

Local Stock Code: Not on Stock



Main

Range of product	Modicon M171
Product or component type	Display module
Display colour	Monochrome
Supply	External source

Complementary

Display type	LCD screen
Number of key	4
Colour	White
[Us] rated supply voltage	12 V DC
Power consumption in W	5 W 0 W
Marking	CE
Realtime clock	With clock
Local signalling	LCD display
Product compatibility	Logic controller M171 optimized
Height	137 Mm
Width	96.5 Mm
Depth	31.3 Mm
Product weight	0.143 Kg

Environment

Product certifications	cURus
IP degree of protection	IP40 front face:

Ordering and shipping details

Category	US1PC1222537
Discount Schedule	PC12
GTIN	3606480752667
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 Cm
Package 1 Width	13.000 Cm
Package 1 Length	18.500 Cm
Package 1 Weight	259.000 G
Unit Type of Package 2	S02
Number of Units in Package 2	6
Package 2 Height	15.000 Cm
Package 2 Width	30.000 Cm
Package 2 Length	40.000 Cm
Package 2 Weight	1.811 Kg
Unit Type of Package 3	P06
Number of Units in Package 3	96
Package 3 Height	75.000 Cm
Package 3 Width	60.000 Cm
Package 3 Length	80.000 Cm
Package 3 Weight	36.976 Kg

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is k
Mercury free	Yes
Sustainable packaging	Yes
Packaging made with recycled cardboard	Yes
REACH Regulation	Reference contains Substances of Very High Concern above the threshold 
EU RoHS Directive	Compliant By Exemption 
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **End of commerc. announced**