



ENGLISH

Datasheet

RS Pro White Nylon Non-Releasable Cable Tie, 100mm x 2.5 mm

RS Stock No: **390-274**



Product Details

RS Pro nylon 66 non-releasable cable tie in white colour, measures 100 x 2.5 mm. A cable tie with an integral identification plate (25 x 8 mm) is manufactured from white nylon 66 which can be marked with hot foil or indelible pens.

**Specifications:**

Colour	White
Fire Behaviour	Flame Retardant
Length	100 mm
Material	Nylon 66
Maximum Bundle Diameter	23 mm
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-50°C
Operating Temperature Range	-50 to +85°C
Product Name	Cable Tie
Quantity	100
Standards Met	UL 94 V-2, cURus, ABS, RoHS Compliant
Tensile Strength	78.4 N
Type	Non-Releasable
Width	2.5 mm