

7058

Product Information



2000 µm double-sided acrylic core tape

Product Description

tesa® ACX^{plus} 705x series is a highly transparent acrylic core tape designed for bonds that achieve a seamless and optical clear finish. Translucent and transparent materials, such as glass or acrylic are easy to bond with tesa® ACX^{plus} 7058.

Product Features

- Transparent acrylic core tape and ideal for bonding transparent / translucent substrate

Application Fields

Exemplary mounting applications in different industries (e.g. extruder, appliances, interior fit-out, signage) include:

- Signage mounting
- Plisse profiles
- Deco panel / glass mounting

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|--------------------|-------------------|-------------|
| • Backing | solid acrylic | • Total thickness | 2000 µm |
| • Type of adhesive | pure acrylic | • Color | transparent |
| • Type of liner | silicone-free film | | |

Adhesion to Values

- | | |
|------------------------|---------|
| • Steel (after 3 days) | 27 N/cm |
|------------------------|---------|

Additional Information

For more technical data please click on the following link to open our technical information sheet:

<https://www.tesa.com/ACX^{plus}/TI-sheet>

The product is recommended for indoor and outdoor usage. To ensure the highest performance possible, our aim is to fully understand the application (including the substrates involved) to provide the best product recommendation.

Liner options:

- PV12: Transparent PET liner – unbranded
- PV26: White paper liner – unbranded
- PV28: Blue film liner – unbranded

For latest information on this product please visit <http://l.tesa.com/?ip=07058>



7058

Product Information

Additional Information

- PV48: White film liner – branded

Certificates:

- ift Rosenheim: DI 02/1-2 2009-03 compatibility of tesa® ACX^{plus} and PVB foil (laminated safety glass)
- tecalia: Safety in use mechanical resistance and stability tests according to ETAG003

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=07058>