

Features

- Specially designed to resist loading & prolong pad life.
- Tightly woven for fast, consistent action without compromising durability.
- Flexible construction ideal for grooves, scratch in channels & other hard to reach areas.
- Suitable for use on a wide range of materials including metals, stainless steel, aluminum, plastics, fibreglass, fibre-reinforced plastics, paint, coatings & fillers.

Non-Woven Roll Medium 100mm x 10m

RS Stock No.: 0757822



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Non-Woven Roll

Provide consistent surface preparation. Ideal for cleaning a wide range of applications. Tightly woven for consistent action without compromising durability. Flexible construction is ideal for grooves, scratch in channels and other hard to reach areas.

- *Suitable for use on Stainless Steel, Metal, Plastic, Aluminium*
- *Flexible construction is ideal for grooves, scratch in channels and other hard to reach areas*

General Specifications

Bond	Synthetic Resin
Type	Non-Woven Roll
Grit	Maroon (Medium)
Grade	A0400
Length	10m
Width	100mm

Stock No.	Grit	Grade	Length	Width
XXX-XXXX 0757820	General Purpose	A0240	10m	100mm
XXX-XXXX 0757822	Medium	A0400	10m	100mm
XXX-XXXX 0757821	Fine	SC1000	10m	100mm

Approvals

Declarations	REACH DoC
---------------------	-----------

Similar Products

Stock No.	Brand	Product Name	Grit	Grade	Length	Width
XXX-XXXX 0757820	RS PRO	Non-woven Roll	General Purpose	A0240	10m	100mm
XXX-XXXX 0757822	RS PRO	Non-woven Roll	Medium	A0400	10m	100mm
XXX-XXXX 0757821	RS PRO	Non-woven Roll	Fine	SC1000	10m	100mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories