

175 2

Pipe wrench

Swedish pattern

Code	ETIM
6437500	EC000842
EAN	UNSPSC
4010886643754	27-11-21-13
Country of origin	eCl@ss
Austria	21-04-03-01
Customs tariff number	
82032000	



Article description

- Acc. to DIN 5234 Form A
- Particularly solid design for high loads
- Head angled 85 °
- GEDORE special chrome-vanadium steel
- Drop-forged
- Fully tempered, teeth additionally inductively hardened
- Self-gripping by teeth offset against direction of rotation
- Roll nut cannot be lost

Article information

Contents (Qty of pieces)	1	Standard	DIN 5234 - Form A
Net weight [kg]	2,55 kg	Design non-sparking	No
Total length [mm]	580 mm	Pipe-Ø [mm]	76 mm
Total width [mm]	90 mm	Pipe-Ø [inch]	2
Total height [mm]	28 mm	Clamping width [mm]	76 mm
Surface	Stove enamelled blue	Hardening process	Induction hardened
Material	Chrome-vanadium steel		