

SACC-DSIV-M12MSB-5CON-L180-SI - Device connector rear mounting



1528206
<https://www.phoenixcontact.com/in/products/1528206>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Pin, straight, M12, coding: B, Rear mounting, Pg9, Solder pins, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239904

Commercial data

Item number	1528206
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	ABQ
Product key	ABQEGL
Catalog page	Page 75 (PC-2005)
GTIN	4046356023184
Weight per piece (including packing)	21 g
Weight per piece (excluding packing)	20.1 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-M12MSB-5CON-L180-SI - Device connector rear mounting



1528206

<https://www.phoenixcontact.com/in/products/1528206>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting Pg9 With locking nut
Assembly note	With locking nut

Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	no
Coding	B
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PBT
Material for screw connection	Brass, nickel-plated

Electrical properties

Contact resistance	$\leq 0.003 \Omega$
Insulation resistance	$\geq 1 T\Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Solder pins
Contact connection type	Pin

Connector

Connection 1

Head design	Pin
-------------	-----

SACC-DSIV-M12MSB-5CON-L180-SI - Device connector rear mounting



1528206

<https://www.phoenixcontact.com/in/products/1528206>

Head cable outlet	straight
Head thread type	M12
Coding	B

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
UL Type Rating	Type 4 (indoor use only)


SACC-DSIV-M12MSB-5CON-L180-SI - Device connector rear mounting

1528206

<https://www.phoenixcontact.com/in/products/1528206>

Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., B-coded, male side

SACC-DSIV-M12MSB-5CON-L180-SI - Device connector rear mounting



1528206
<https://www.phoenixcontact.com/in/products/1528206>

Classifications

ECLASS

ECLASS-13.0	27440109
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-M12MSB-5CON-L180-SI - Device connector rear mounting



1528206

<https://www.phoenixcontact.com/in/products/1528206>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fad3fb72-946c-420f-aade-cea12d24434a

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in