

Increase in module height 3VA12 (250 A), W: 600 mm 3 or 4-pole,



Model	
product brand name	SIVACON S4
product designation	vertical module increase
design of the product	3VA12 (up to 250 A)
design of the surface	zinc plated
General technical data	
design	assembly kit
suitability for use	for 3VA molded-case circuit breakers
RAL color number	other
color	miscellaneous
Product details	
product component	
• cable entry	No
• lock	No
Mechanical Design	
height	50 mm
width	600 mm
depth	400 mm
installation width for cabinet installation	600 mm
installation depth for cabinet installation	400 mm
shape of inner subdivisions	
• shape 2a	No
• shape 2b	No
• shape 3a	Yes
• shape 3b	Yes
• shape 4a	No
• shape 4b	No
mounting position	horizontal
material	sheet-steel
Certificates	
reference code according to IEC 81346-2	UC
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



EG-Konf.



VDE



[Confirmation](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ5000-4BA60>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ5000-4BA60>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ5000-4BA60

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

7/24/2023 

