



Fuse-link, high speed, 5 A, AC 240 V, DC 200 V, 100 kA, BS88, 8 x 48 mm, aR, BS

Part no. **5AMP 240V AC BS88 FUSE**
Catalog No. **GSA5**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	5
Rated voltage			AC 240 V DC 200 V
Construction size			BS88
Size			8 x 48 mm
Utilization category			aR
Breaking Capacity		kA	100
usable for size/applications			Protection of semi-conductor devices
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-4

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	5
Rated voltage		V	240
Voltage type			AC/DC
Rated switching capacity		kA	100
Utilization category			aR (accompanied semiconductor protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No