



NC4FXX

4 pole female cable connector with Nickel housing and silver contacts.

The next generation of the worldwide accepted standard of XLR cable connectors. The successor of the X series offers several new features which make it more reliable, easier to assemble and improves contact integrity as well cable strain relief.

Features & Benefits

- ✓ Unique cage design of female contact for low contact resistance and high integrity
- ✓ Female contact incorporates a solder barrier to prevent solder running into the contact mating area
- ✓ Female connector with improved solid metal latch which is larger and easier to handle
- ✓ Additional ground spring contacts for better shell ground continuity
- ✓ Improved chuck type strain relief provides higher pull-out force and makes assembly easier and faster
- ✓ Boot with polyurethane gland gives high protection to cable bending stresses
- ✓ Colored rings and boots available for coding or identification
- ✓ Sleek and ergonomic design - valuable and handy
- ✓ Rugged zinc diecast shell, longlasting and dependable
- ✓ Internal thread on shell is well protected against any damage

Technical Information

Product	
Title	NC4FXX
Connection Type	XLR
Gender	female

Electrical	
Capacitance between contacts	$\leq 7 \text{ pF}$
Contact resistance	$\leq 3 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	10 A
Rated voltage	$< 50 \text{ V}$

Mechanical	
Cable O.D.	3.5 - 8.0 mm
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	max. 1.5 mm^2
Wiresize	max. 16 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	Polyurethan
Contact plating	2 µm Ag over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA66)
Locking element	Zinc diecast (ZnAl4Cu1) / Ck 67 (spring)
Locking element plating	Nickel
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Strain relief	Polyacetal (POM)

Environmental	
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C