


## C5AD06UXXX

(M12 Cordset, 5 Position, 22 AWG Shielded, Male Straight to Female Right Angle)





- Mueller's C5AD06UXXX is an M12 5-pin double ended, shielded instrumentation cable with a straight male connector on one end and a right angle female at the other.
- Keyway A Coding
- Utilizes a 5-conductor 22 AWG PVC-insulated, shielded cable.
- Ratings:
  - o Current: 4 A
  - Voltage: 250 V AC/DC
- Material:
  - Coupling Nuts Nickel Plated Brass
  - Pins/Contacts Gold Plated Brass
- Length: The "U" in the model number represents unit of measurement. Either: Meters (M), Feet (F)
- Length: The "XXX" in the model number represents length. Standard lengths are 2, 5, and 10 meters. Any other lengths available upon request.
- Meets Standard: IEC 61076-2-101
- Protection Class: IEC IP68
- RoHS 3 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524