



Datasheet

ENGLISH

Stock No: 235-679

RS Pro Incandescent Beacon, Rotating, Surface Mount, 12 V dc, 24 V dc



Image representative of range

Product Details

Rotating Filament Beacons

Weatherproof and dustproof to IP56 these beacons offer high quality solutions for industrial environments and process applications.

- High protection rating of IP56
- Magnetic version is rated to 70mph
- Optional cage guard for three-point mounting versions
- Surge protection for safety against peak voltage
- Full internal suppression for maximum interference reduction
- 166mm diameter footprint
- 125 rotations per minute



ENGLISH

Note

Lens must be purchased separately

Supplied with

Appropriate SES (E14) 60W bulb (except the 12/24V versions, which are **not** supplied with a bulb)

Specifications:

Supply Voltage	12 V dc, 24 V dc
Light Effect	Rotating
Lens Colour	Lens Not Included
Mounting Style	Surface Mount
Bulb Type	Incandescent
Current Type	DC
Base Diameter	166mm
Housing Colour	Black
Lamp Included	Yes
Series	V10993
Height	207mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C