

FEATURES

- **Sintered Bronze Material:** Provides high wear resistance and longevity.
- **Flanged Design:** Ensures easy installation and secure positioning.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying load conditions.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **Outside Diameter of 38.06 mm:** Fits standard housings for easy integration.
- **Bore Size of 32.03 mm:** Compatible with a wide range of shafts.
- **Width of 25 mm:** Offers stability and support.

RS PRO 32.03 mm Flanged Plain Bearing

RS Stock No: 558-484



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. The bearing's primary benefit is its ability to support both dynamic and static loads effectively.

General Specifications

Bore Size	32.03 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	38.06 mm
Width	25 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

