PLUG ASSY SIZE 5 ACTIVE

AMPLIMITE

TE Part # 1658641-3 TE Internal #: 1658641-3

View on TE.com >



Connectors > D-Shaped Connectors > D-Sub Connectors > Crimp D-Sub Connectors











Connector Style: Plug

Connector System: Cable-to-Cable

Number of Positions: 50

Contact Size: **20**Shell Size: **5**

Features

Product Type Features

Grade	Standard
Grounding Indents	Without
Product Type	Connector
Shell Type	Full Metal Shell
Connector Style	Plug
Connector System	Cable-to-Cable
Shell Size	5
Shielded	No
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Configuration Features	
Number of Positions	50
Body Features	
Shell Material	Steel
Shell Plating Material	Zinc



Insert Material	Glass-Filled Nylon
Contact Features	
Contact Size	20
Mechanical Attachment	
Mating Connector Lock	With
Mating Connector Lock Type	Mounting Holes
Housing Features	
Housing Material	Nylon GF, Polyester GF
Housing Color	Black
Centerline (Pitch)	2.74 mm, 2.76 mm, 2.79 mm[.108 in][.109 in] [.11 in]
Dimensions	
Cable Insulation Diameter Range	4.58 – 11.68 mm
Wire Size	.2 – .56 mm²
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
Insert Flammability Rating	UL 94V-0
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Package
Packaging Quantity	225
Other	
Comment	Plugs accept size 20 DF pin contacts.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

TE Part # 1658641-3 TE Internal #: 1658641-3




EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JUN 2018 (191)
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.



Customers Also Bought

TE Part # 1658641-3 TE Internal #: 1658641-3





TE Part #5205732-1 CLAMSHELL ASSEMBLY, SIZE 5



TE Part #1658640-2 RECP. ASSEMBLY SIZE 5




TE Part #5748676-5
DIE CAST CBL CLMP KIT,
SZ 5



TE Part #205210-8
PLUG ASSY SIZE 4




TE Part #205209-7 RECP ASSY SIZE 4



TE Part #5205980-1 SCREW RETAINER KIT









Documents

Product Drawings
PLUG ASSY SIZE 5

English

CAD Files

Customer View Model

ENG_CVM_CVM_1658641-3_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1658641-3_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1658641-3_D.3d_stp.zip

English

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

PLUG ASSY SIZE 5

TE Part # 1658641-3 TE Internal #: 1658641-3



English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English