

Zarges Heavy Duty Platform Steps

Max Load: 250kg - (39.4 Stone)



Z600 heavy-duty stepladder

- Strong ZARGES quality flanging connects rung and stile
- Rungs and stiles made from extruded aluminum sections
- Large standing platform (250 mm x 250 mm) made from extruded aluminum sections
Practical aluminum storage tray for small items and tools
- Replaceable 2-component plastic end caps ensure positioning without risk of slipping and at the same time provide firm seating in the stile
- Wide aluminum alloy rungs, 60 mm deep, with non-slip ribbing
- Black, wear-resistant anodized stiles
- High-strength Perlon belts prevent splay, on models with 4 rungs or more
- Max. Load 250 kg

RS Code	Zarges Code	No. of Treads	Overall Length (m)	Platform Height (m)	Working Height (m)	Weight (KG)
8332841	41145	3	1.59	0.8	2.8	7.7
8332850	41146	4	1.87	1.06	3.1	9.00
8332853	41147	5	2.15	1.33	3.35	9.70
8332857	41148	6	2.43	1.59	3.60	10.60
8332866	41149	8	2.99	2.12	4.15	11.70