



REV	DESCRIPTION	DATE
-----	-------------	------

NOTE:

1. MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16
AMP.	3	4	7	10
2. MAXIMUM ELECTRICAL RATING:
125°C 300 VOLTS MAX.
3. INSULATION MATERIAL: PC
4. INSULATION COLOR: RED
5. TERMINAL MATERIAL: COPPER
6. WIRE RANGE: 22-16 A.W.G. (0.5-1.5mm²)
7. TERMINAL THICKNESS: 0.30mm

Tolerance Unless Otherwise Specified	
0 >	MM ± ANGLE
>	MM ± 0° REF ±
>	MM ± ° ±
>	MM ± ° ±

NAME	PC-INSULATED FEMALE DISCONNECTORS				UNIT	mm	
PART NO.	FDN11-110(8)	MATERIAL			APPROVE		
NUMBER	TNV-468	SCALE	SHEET	PAGE	CHECKED		
DATE	09/07/2005	4 : 1	1-0	1 OF 1	DRAWN		