


Features

- Thermoresistances
- Max. operating temperature 400°C
- Protection tube AISI304 (DIN1.4301)
- Sensor type DIN/EN60751
- Fiber glass + fiber glass + braided wire
- Immersion Length 26mm
- Tube Diameter 9,4mm
- Cable Length: 2m

RS PRO Bayonet Type Cable Lug PT-100 Thermoresistances

RS Stock No: 0350413



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Standard Bayonet Type PT100 Thermoresistances Temperature Sensor

Diameter(M): 9,4mm

Immersion Length(L): 26mm

Cable Length(K): 2m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


General Specifications

Max. Operating Temperature	-50 °C / +400 °C
Standard cable types	Fiber glass + fiber glass + braided wire
Sensor type	DIN/EN60751 Class "B"
Protection tube material	AISI304 (DIN1.4301) Standard production

Mechanical Specifications

Diameter (M)	9,4mm
Immersion Length (L)	26mm
Cable Length (K)	2m

Electrical Connection



PT-100 Connections

