




# PRODUCT DATASHEET

Datasheet creation date: 2025/07/08 5:11 (UTC)



## 6001VV

### Single-Row Deep Groove Ball Bearings

#### Parts Number

6001VVC3
----------

#### Boundary Dimensions

d	12	mm	Bore diameter
D	28	mm	Outside diameter
B	8	mm	Width
r (min.)	0.3	mm	Chamfer dimension

#### Basic Load Ratings

Cr	5600	N	Basic dynamic load rating
C0r	2370	N	Basic static load rating

#### Speeds

Grease	32000	min-1	Grease lubrication
--------	-------	-------	--------------------

#### Abutment and Fillet Dimensions

da (min.)	14	mm	Diameter of shaft abutment
da (max.)	15.5	mm	Diameter of shaft abutment
Da (max.)	26	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

#### Calculation factors

fo	13	Factor
----	----	--------

#### Additional information

z	8	Number of Balls	
Dw	4.762	mm	Ball Diameter

#### Mass

Mass approx.	0.022	kg	Mass approx.
--------------	-------	----	--------------

