



Foot protection

ORGANO S4 FO

FOOD INDUSTRY

Robust safety boot with wide studs for optimum protection



Specific benefits



Comfort

- Shock-absorbing heel to relieve joint strain



Easy to use

- Rear lug for easy removal
- Textured upper for easy donning



Durability

- Sustainable materials

Certifications and norms



EN ISO 20345

S4 FO A E

Applications

- Manufacturing/Transformation
- Accomodation & Food services
- Food & Beverage
- Cleanliness
- Temporary work
- Storage

Protects against risks



Antistatic



Shock



Slip



Weather



ORGANO S4 FO

FOOD INDUSTRY

Robust safety boot with wide studs for optimum protection

Foot protection

Standards - Details

Technical details

Shoe type	Boot
Outsole material	Nitrile, PVC
Anti-perforation insert	None
Upper material	PVC
Upper height size 42 (cm)	38
Calf circumference (cm)	47
Safety toe-cap	Stainless steel
Lining material	Textile, Polyester
Weight (g per shoe)	1100
Size range	37 → 47



ORGANO S4 FO

FOOD INDUSTRY

Robust safety boot with wide studs for optimum protection

Safety footwear

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
ORGANS4BC37	White-Grey	37	ORGANO S4 FO	3295249261405	13295249261402	6	1	12.5 kg	40.2 cm	40.2 cm	40.2 cm
ORGANS4BC38	White-Grey	38	ORGANO S4 FO	3295249258368	13295249258365	6	1	12.4 kg	40.2 cm	40.0 cm	40.6 cm
ORGANS4BC39	White-Grey	39	ORGANO S4 FO	3295249259792	13295249259799	6	1	13.3 kg	40.0 cm	40.0 cm	40.6 cm
ORGANS4BC40	White-Grey	40	ORGANO S4 FO	3295249259808	13295249259805	6	1	13.3 kg	40.2 cm	39.8 cm	40.4 cm
ORGANS4BC41	White-Grey	41	ORGANO S4 FO	3295249259815	13295249259812	6	1	14.1 kg	40.8 cm	39.8 cm	40.4 cm
ORGANS4BC42	White-Grey	42	ORGANO S4 FO	3295249259822	13295249259829	6	1	14.3 kg	40.2 cm	40.0 cm	40.6 cm
ORGANS4BC43	White-Grey	43	ORGANO S4 FO	3295249259839	13295249259836	6	1	14.6 kg	40.8 cm	39.2 cm	40.6 cm
ORGANS4BC44	White-Grey	44	ORGANO S4 FO	3295249259846	13295249259843	6	1	15.5 kg	41.4 cm	39.6 cm	40.6 cm
ORGANS4BC45	White-Grey	45	ORGANO S4 FO	3295249259853	13295249259850	6	1	15.8 kg	40.8 cm	39.6 cm	40.2 cm
ORGANS4BC46	White-Grey	46	ORGANO S4 FO	3295249259860	13295249259867	6	1	16.1 kg	40.8 cm	39.6 cm	40.8 cm
ORGANS4BC47	White-Grey	47	ORGANO S4 FO	3295249259877	13295249259874	6	1	16.8 kg	42.2 cm	41.0 cm	49.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height