


FEATURES

- **Non-Dimmable:** Ensures consistent light output without fluctuations
- **1 A Driver Current:** Supports efficient power delivery to connected LEDs
- **198-264 V AC Input Voltage:** Compatible with a wide range of AC power sources
- **IP67 Rated:** Offers excellent protection against dust and water, suitable for harsh environments
- **Constant Voltage Operation:** Provides stable voltage output for reliable LED performance
- **Single Output:** Simplifies installation and reduces wiring complexity

RS PRO 24W LED Driver, 24V Constant Voltage

RS Stock No: 642-782



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 24W LED Driver is designed to provide reliable power to LED lighting systems. With a constant voltage output of 24V, it ensures stable performance for a variety of LED applications. Its robust design and IP67 rating make it suitable for both indoor and outdoor use, offering protection against dust and water ingress.

General Specifications

Dimming Operation	Non-Dimmable
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

Electrical Specifications

Driver Current	1 A
Input Voltage	198-264 V ac
Input Voltage Type	AC
Maximum Output Power	24 W
Output Voltage	24 V

Protection Category

IP Rating	IP67
-----------	------

Approvals

Standards/Approvals	CE, EEN 55015, EN 61000-3-2, EN 61000-3-3, EN 61547, EN61000-4-2,3,4,5,6,8,11, EN61347-1, EN61347-2-13
---------------------	--