

Datasheet

RS Pro 1 Port Serial Board

RS Stock No: **665-4644**



Product Details

RS Pro 1 port serial board has female BNC and RJ45 connectors. This serial board measuring 120 x 55 x 17 mm, has a Ethernet RJ45 - BNC network converter. The external power supply rated at 110 / 230 V ~ 12 V dc, 1 A. The operating temperature ranges from 0 to 55°C.

Features and Benefits

- Measures 120 x 55 x 17 mm
- Maximum transmission speed of 10 Mbps
- 1 port
- IEEE-802.3 10Base-T, 10Base-2 standards
- Compact (metal housing)



ENGLISH

Specifications:

Number of Ports

1