

316RS5

Wall mounted socket

2CMA193105R1000



Wall mounted socket, earthing sleeve position 5h, rated current 16A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Black

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA193105R1000
Function	Wall mounted socket
EAN	73926969352
Catalog Description	Surface socket-outlet, cI5, 16A, IP44, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421205
E-Number Norway	1542319
E-Number Sweden	E2416448
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	ERS
Color	Black
Number of Poles	4
Clock Position	5Hour
Rated Current	16 ampere
Rated Voltage	600 ... 690 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	79 millimetre
Product Net Length	132 millimetre
Product Net Depth	132 millimetre
Product Net Weight	0.24 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.4 kilogram
Package Length	182 millimetre
Package Units	box 10 piece